



|                                                                                   | Dimensiones molduras (mm)                                                                                                    | 7x12                                                                              | 10x16                                                                              | 10x22                                                                               | 10x30                                                                               |
|-----------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
|                                                                                   | <p><b>Blanco</b><br/>RAL 9010<br/>(ref. 78xxx-2<br/>y ref. 78xxx-2A)</p> <p><b>Gris</b><br/>RAL 7035<br/>(ref. 78xxx-04)</p> |  |  |  |  |
|  | <p><b>Molduras sin tabique</b><br/>2 m</p> <p><b>Molduras autoadhesivas</b><br/>2 m</p>                                      | <b>78010-2</b>                                                                    | <b>78021-2</b>                                                                     | <b>78022-2</b>                                                                      | <b>78023-2</b>                                                                      |
|  | <b>Molduras con tabique</b><br>2 m                                                                                           |                                                                                   |                                                                                    |                                                                                     |                                                                                     |

### Elementos de acabado en **U24X**

|                                                                                     |                        |  |                |                |
|-------------------------------------------------------------------------------------|------------------------|--|----------------|----------------|
|    | <b>Ángulo plano</b>    |  | <b>78222-2</b> | <b>78223-2</b> |
|  | <b>Ángulo exterior</b> |  | <b>78272-2</b> | <b>78273-2</b> |
|  | <b>Ángulo interior</b> |  | <b>78322-2</b> | <b>78323-2</b> |
|  | <b>Tapa final</b>      |  | <b>78372-2</b> | <b>78373-2</b> |
|  | <b>Derivación</b>      |  | <b>78472-2</b> | <b>78473-2</b> |
|  | <b>Cubrejuntas</b>     |  | <b>78522-2</b> | <b>78523-2</b> |




### Cajas de conexión y derivación en **U24X**

|                                                                                     |                          |  |                |
|-------------------------------------------------------------------------------------|--------------------------|--|----------------|
|  | 70x70x27 mm              |  | <b>78455-2</b> |
|  | 85x85x45 mm              |  | <b>71451-2</b> |
|  | 110x110x45 mm            |  | <b>78457-2</b> |
|  | 110x150x74 mm            |  | <b>73461-2</b> |
|  | Se incluyen 2 tornillos. |  | <b>78503-2</b> |

### Elementos de fijación en **U63X**

|                                                                                     |                                                       |  |              |
|-------------------------------------------------------------------------------------|-------------------------------------------------------|--|--------------|
|  | <p><b>Taco para canales</b><br/>Usar broca Ø4 mm.</p> |  | <b>25104</b> |
|-------------------------------------------------------------------------------------|-------------------------------------------------------|--|--------------|



|  | 16x16                                                                             | 16x30                                                                                                                                                                  | 16x50                                                                             | 20x30                                                                                                                                                                  | 20x50                                                                                                                                                                      | 20x75                                                                               |
|--|-----------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
|  |  | <br> |  | <br> | <br> |  |
|  | <b>78031-2</b><br><b>78031-04</b>                                                 | <b>78033-2</b>                                                                                                                                                         |                                                                                   | <b>78043-2</b><br><b>78043-04</b>                                                                                                                                      | <b>78045-2</b>                                                                                                                                                             |                                                                                     |
|  | <b>78031-2A</b>                                                                   | <b>78033-2A</b>                                                                                                                                                        |                                                                                   |                                                                                                                                                                        |                                                                                                                                                                            |                                                                                     |
|  |                                                                                   |                                                                                                                                                                        | <b>78083-2</b>                                                                    | <b>78085-2</b>                                                                                                                                                         | <b>78093-2</b>                                                                                                                                                             | <b>78095-2</b>                                                                      |

|                                   |                |                |                                   |                |                |
|-----------------------------------|----------------|----------------|-----------------------------------|----------------|----------------|
| <b>78231-2</b><br><b>78231-04</b> | <b>78233-2</b> | <b>78235-2</b> | <b>78243-2</b><br><b>78243-04</b> | <b>78245-2</b> | <b>78247-2</b> |
| <b>78281-2</b><br><b>78281-04</b> | <b>78283-2</b> | <b>78285-2</b> | <b>78293-2</b><br><b>78293-04</b> | <b>78295-2</b> | <b>78297-2</b> |
| <b>78331-2</b><br><b>78331-04</b> | <b>78333-2</b> | <b>78335-2</b> | <b>78343-2</b><br><b>78343-04</b> | <b>78345-2</b> | <b>78347-2</b> |
| <b>78381-2</b><br><b>78381-04</b> | <b>78383-2</b> | <b>78385-2</b> | <b>78393-2</b><br><b>78393-04</b> | <b>78395-2</b> | <b>78397-2</b> |
| <b>78481-2</b>                    | <b>78483-2</b> | <b>78485-2</b> | <b>78493-2</b>                    | <b>78495-2</b> | <b>78497-2</b> |
| <b>78531-2</b><br><b>78531-04</b> | <b>78533-2</b> | <b>78535-2</b> | <b>78543-2</b><br><b>78543-04</b> | <b>78545-2</b> | <b>78547-2</b> |

|  |                     |         |                     |         |  |
|--|---------------------|---------|---------------------|---------|--|
|  | 78455-2             |         |                     |         |  |
|  | 71451-2             |         |                     |         |  |
|  | 78457-2<br>78457-04 | 78457-2 | 78457-2<br>78457-04 | 78457-2 |  |
|  | 73461-2<br>73461-04 | 73461-2 | 73461-2<br>73461-04 | 73461-2 |  |
|  | 78503-2             | 78507-2 | 78503-2             | 78507-2 |  |

|              |  |  |  |  |  |
|--------------|--|--|--|--|--|
| <b>25104</b> |  |  |  |  |  |
|--------------|--|--|--|--|--|